

www.ropanamedicure.com



ROPCRYL 910 FAST

Braided & Coated Polyglactin 910 Absorbable Surgical Suture Synthetic



Suture Material:

Braided & Coated Polyglycolic 910 (Absorbable Surgical Suture USP)

Raw Material Description:

Polyglycolic Acid is a synthetic polymer composed of homopolymers of Glycolide (100%).

Coating:

Poly (glycolide-ce-L-Lactide) & Calcium Stearate.

Material Color & Specifications:

Undyed.

Features:

- Minimal tissue reaction and has an excellent handling properties.
- Coating ensures Smooth tissue passage.
- ROPCRYL FAST 910 sutures absorption takes place through hydrolysis completely in 40 to 45 days.
- 75% of Tensile Strength is retained for 3 days and 50% till 5 days.

Sterilization:

Ethylene Oxide

Packing & Availability:

Dry & Sterile Suture

Primary packing:

Each Suture is wound and packed in a leakproof Aluminum Foil pouch.

Each such aluminum pouch is further packed in a peelable overwrap pouch made of Medical Grade Paper and Laminated Polyethylene film.

Secondary packing:

12 such suture pouches packed in an outer printed carton box.

USP Sizes available:

USP 6/0 to USP 2.

Availability:

- With needle, Suture lengths from 45 cm to 180cm & Needle length from 12mm to 50mm
- Includes variety of Stainless Steel needles like Round bodied, Cutting, Reverse cutting, Taper cutting, Trocar Point etc.





ROPCRYL 910 FAST

Braided & Coated Polyglactin 910 Absorbable Surgical Suture U.S.P.



PPRODUCT CODE	SUTURE		
	USP SIZE	LENGTH	NEEDLE DESCRIPTION & LENGTH
RN 2763FS	0	100cm	1/2 Circle TC, 35mm
RN 2763	0	90cm	1/2 Circle TC, 35mm
RN 2763RB	0	100	1/2 Circle RB, 30mm
RN 2760	2-0	75cm	3/8 Circle RC, 26mm
RN 2762DY	2-0	90cm	1/2 Circle Cutting-DA, 30mm
RN 2762RB	2-0	110cm	1/2 Circle RB, 35mm
RN 2762FS	2-0	100cm	1/2 Circle TC , 35mm
RN 2777	2-0	140cm	1/2 Circle RC & 1/2 Circle RB-DA, 36mm
RN 2762	2-0	90cm	1/2 Circle TC, 35mm
RN 2761RB	2-0	90cm	1/2 Circle RB, 38mm
RN 2761	2-0	100cm	1/2 Circle TC, 35mm
RN 2764	2-0	100cm	1/2 Circle RB, 40mm
RN 2516	3-0	90cm	1/2 Circle RB, 35mm
RN 2732	3-0	75cm	3/8 Circle RC, 26mm
RN 2739	3-0	70cm	1/2 Circle RB, 30mm
RN 2718	4-0	45cm	3/8 Circle Cutting, 16mm
RN 2718RB	4-0	45cm	3/8 Circle RB, 16mm

Q